



KRA2007KU_Serie

Werkstatt- Rollwagen

Bewährte, robuste Konstruktion jetzt in verschiedenen Farben

Merkmale und Vorteile

- Robuste, verwindungssteife Konstruktion
- Rollengelagerte Schubladen
- Zentralverriegelung mit Tubular- Sicherheitszylinderschloss
- Schubladenverriegelungsmechanismus Lock`n Roll
- Pulverbeschichtete Oberfläche
- Schwerlastrollen mit Feststellbremse



KRA2007KUZGG

Art.-Nr.	Beschreibung
KRA2007KUPPS	Candy Apple Red w/Black Trim
KRA2007KUPOT	Flat Black w/Black Trim
KRA2007KUZGG	Shock Blue w/Black Trim
KRA2007KUPWZ	Storm Grey w/Black Trim
KRA2007KUPYA	Pink w/Black Trim
KRA2007KUPEG	Purple w/Black Trim
KRA2007KUPLE	Arctic Silver w/Black Trim
KRA2007KUPKG	Extreme Green w/Black Trim
KRA2007KUPKH	Electric Orange w/Black Trim
KRA2007KUPDO	Yellow w/Black Trim
KRA2007KUPDC	White w/Black Trim
KRA2007KUPZR	Combat Green w/Black Trim
KRA2007KUZAT	Teal w/Black Trim
KRA2007KUPVF	Midnight Blue w/Titanium Trim
KRA2007KU	Standard Red/Bright Silver Trim (o. Abb.)
KRA2007KUPC	Gloss Black/ Bright Silver Trim
KRA2007KUPCM	Royal Blue/ Bright Silver Trim

Bright Silver Trim Black Trim

Candy Apple Red with Black Trim KRA2007KUPPS	Flat Black with Black Trim KRA2007KUPOT	Shock Blue with Black Trim KRA2007KUZGG	Storm Grey with Black Trim KRA2007KUPWZ
Extreme Green with Black Trim KRA2007KUPKG	Electric Orange with Black Trim KRA2007KUPKH	Yellow with Black Trim KRA2007KUPDO	White with Black Trim KRA2007KUPDC
Pink with Black Trim KRA2007KUPYA	Purple with Black Trim KRA2007KUPEG	Arctic Silver with Black Trim KRA2007KUPLE	Royal Blue Bright Silver KRA2007KUPCM
Combat Green with Black Trim KRA2007KUPZR	Teal with Black Trim KRA2007KUZAT	Midnight Blue with Titanium Trim KRA2007KUPVF	Gloss Black Bright Silver KRA2007KUPC

Ladefähigkeit (kg)	498
Lagerfläche (m ²)	1.7
Lagervolumen (m ³)	0.154
Breite (mm)	680
Tiefe (mm)	500
Höhe (mm)	951
Schubladen gesamt (Anzahl)	7
Belastbarkeit Rollenlager (kg)	45

- ⚠️ WARNUNG**
- Nicht mehr als eine Schublade gleichzeitig öffnen.
 - Von Kindern fernhalten.
 - Vor dem Transport Schubladen, Deckel und Türen verriegeln und abschließen.
 - Im Stand Bremsen an den Rädern betätigen.
 - Nicht auf oder in geöffnete Schubladen treten.
 - Beim Transport nicht wegstoßen oder wegrollen lassen.
 - Beim Anheben Handschuhe aufsetzen..
 - Beim Transport/Verladung auf Finger und Füße achten.
 - Bedienungsanleitung und zusätzliche Sicherheitshinweise beachten.

